

# PURETECH

PVO200X50-Ø20

EAN 4031582321227  
Broj porudžbine 00050594

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja	● ● ○ ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	205 kg
Statički Nosivost	410 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	1,155 kg

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovina	20,1 mm
dužina glavcine	58 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

# PURETECH

PVO200X50-Ø20

EAN 4031582321227  
Broj porudžbine 00050594



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

