

PURETECH

DVR125X37-Ø12

EAN 4031582070064
Broj porudžbine 00030521

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	37 mm
dimenzija rupa osovine	12 mm
dužina glavnice	44,4 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,577 kg

PURETECH

DVR125X37-Ø12

EAN 4031582070064
Broj porudžbine 00030521



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

