

BASETECH

POO125X40-Ø12 RAL9011

EAN 4031582320756
Order number 00029804



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.177 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	12 mm
Hub length	44 mm
Hardness of tread (D)	65 Shore D

BASETECH

POO125X40-Ø12 RAL9011

EAN 4031582320756
Order number 00029804



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

