

PURETECH

DIR125X37-Ø12

EAN 4031582317763
Order number 00030519



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.46 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.26 lb

PURETECH

DIR125X37-Ø12

EAN 4031582317763
Order number 00030519



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

