

SUPRATECH

PJO125X32-Ø12

EAN 4031582070231
Order number 00003187



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.199 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	32 mm
Axle hole diameter	12.3 mm
Hub length	34.9 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJO125X32-Ø12

EAN 4031582070231
Order number 00003187



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

