

# SUPRATECH

PJO125X32-Ø12

EAN 4031582070231  
Order number 00003187



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.44 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.26 in
Axle hole diameter	0.48 in
Hub length	1.37 in
Hardness of tread (A)	87 Shore A

# SUPRATECH

PJO125X32-Ø12

EAN 4031582070231  
Order number 00003187



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

