

MAXTECH

UAP200X32-Ø8

EAN 4031582323023
Order number 00026927



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	1.71 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.26 in
Axle hole diameter	0.32 in
Hub length	1.44 in
Hardness of tread (D)	40 Shore D

MAXTECH

UAP200X32-Ø8

EAN 4031582323023
Order number 00026927



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

