

MAXTECH

UAP200X32-Ø8

EAN 4031582323023

Broj porudžbine 00026927



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	32 mm
dimenzija rupa osovina	8,1 mm
dužina glavcine	36,5 mm
Teškoća gazećeg omotac (D)	40 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	160 kg
Statički Nosivost	320 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,777 kg

MAXTECH

UAP200X32-Ø8

EAN 4031582323023
Broj porudžbine 00026927



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

