

PURETECH

DIR100X30-Ø12

EAN 4031582317756
Order number 00004913



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Roller bearing |
| Threadguards | Without threadguard |
| Diameter | 3.94 in |
| Tread width | 1.18 in |
| Axle hole diameter | 0.47 in |
| Hub length | 1.75 in |
| Hardness of tread (A) | 80 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Puretech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 154.32 lb |
| Load capacity Static | 308.65 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 185 °F |
| Overall weight | 0.61 lb |

PURETECH

DIR100X30-Ø12

EAN 4031582317756
Order number 00004913



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

