

PURETECH

DIR100X30-Ø12

EAN 4031582317756

Broj porudžbine 00004913



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	30 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	70 kg
Statički Nosivost	140 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,278 kg

PURETECH

DIR100X30-Ø12

EAN 4031582317756
Broj porudžbine 00004913



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

