

MAXTECH

UAO050X20-Ø8

EAN 4031582322842
Order number 00003565



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	110.23 lb
Load capacity Static	220.46 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.06 lb

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.79 in
Axle hole diameter	0.33 in
Hub length	0.83 in
Hardness of tread (D)	40 Shore D

MAXTECH

UAO050X20-Ø8

EAN 4031582322842
Order number 00003565



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

