

BASETECH

POI050X20-Ø6

EAN 4031582320701
Order number 00050768



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	35 kg
Load capacity Static	70 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.016 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	50 mm
Tread width	20 mm
Axle hole diameter	6.1 mm
Hub length	21.7 mm
Hardness of tread (D)	65 Shore D

BASETECH

POI050X20-Ø6

EAN 4031582320701
Order number 00050768



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

