

# DURATECH

U00050X20-Ø8

EAN 4031582323450  
Order number 00006518



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	121.25 lb
Load capacity Static	242.51 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.04 lb

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.79 in
Axle hole diameter	0.32 in
Hub length	0.85 in
Hardness of tread (D)	75 Shore D

# DURATECH

U00050X20-Ø8

EAN 4031582323450  
Order number 00006518



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

