

BASETECH

POO065X30-Ø12 RAL9011

EAN 4031582320718
Order number 00012004



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Threadguards | Without threadguard |
| Diameter | 65 mm |
| Tread width | 30 mm |
| Axle hole diameter | 12.1 mm |
| Hub length | 34.5 mm |
| Hardness of tread (D) | 65 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Basetech |
| Housing type | Wheel |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 120 kg |
| Load capacity Static | 240 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 0.047 kg |

BASETECH

POO065X30-Ø12 RAL9011

EAN 4031582320718
Order number 00012004



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

