

# PURETECH

PVO125X37-Ø12

EAN 4031582321203  
Order number 00001078



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	37 mm
Axle hole diameter	12 mm
Hub length	44 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.453 kg

# PURETECH

PVO125X37-Ø12

EAN 4031582321203  
Order number 00001078



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

