

# MAXTECH

XSP200X32-Ø8

EAN 4031582323689  
Order number 00002022



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.789 kg

## WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	32 mm
Axle hole diameter	8.1 mm
Hub length	36.5 mm
Hardness of tread (D)	46 Shore D

## HOUSING

Electric conductive	✓
---------------------	---

# MAXTECH

XSP200X32-Ø8

EAN 4031582323689  
Order number 00002022



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

