

MAXTECH

XSP200X32-Ø8

EAN 4031582323689
Order number 00002022



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall weight	1.74 lb

WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.26 in
Axle hole diameter	0.32 in
Hub length	1.44 in
Hardness of tread (D)	46 Shore D

HOUSING

Electric conductive	✓
---------------------	---

MAXTECH

XSP200X32-Ø8

EAN 4031582323689
Order number 00002022



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

