

SUPRATECH

PJO050X19-Ø8

EAN 4031582070033
Order number 00003750



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.05 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.75 in
Axle hole diameter	0.32 in
Hub length	0.83 in
Hardness of tread (A)	87 Shore A

SUPRATECH

PJO050X19-Ø8

EAN 4031582070033
Order number 00003750



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

