

ELASTECH

UEP200X46-Ø12

EAN 4031582070378
Order number 00024579



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	46 mm
Axle hole diameter	12.5 mm
Hub length	60 mm
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	1.312 kg

ELASTECH

UEP200X46-Ø12

EAN 4031582070378
Order number 00024579



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

