

# ELASTECH

UEP200X46-Ø12

EAN 4031582070378  
Order number 00024579



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	881.85 lb
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	2.89 lb

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	7.87 in
Tread width	1.81 in
Axle hole diameter	0.49 in
Hub length	2.36 in
Hardness of tread (A)	63 Shore A

# ELASTECH

UEP200X46-Ø12

EAN 4031582070378  
Order number 00024579



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

