

ELASTECH

UER200X46-Ø20

EAN 4031582323337
Broj porudžbine 00023477

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	46 mm
dimenzija rupa osovina	20 mm
dužina glavcine	58 mm
Teškoća gazećeg omotac (A)	63 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	400 kg
Statički Nosivost	800 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,11 kg

ELASTECH

UER200X46-Ø20

EAN 4031582323337
Broj porudžbine 00023477



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

