

ELASTECH

UEP160X46-Ø12

EAN 4031582070361
Order number 00025058



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	160 mm
Tread width	46 mm
Axle hole diameter	12.5 mm
Hub length	60 mm
Hardness of tread (A)	63 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.929 kg

ELASTECH

UEP160X46-Ø12

EAN 4031582070361
Order number 00025058



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

