

ELASTECH

UFP160X46-Ø12

EAN 4031582323368
Order number 00024982



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	661.39 lb
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	176 °F
Overall weight	2.08 lb

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.81 in
Axle hole diameter	0.49 in
Hub length	2.36 in
Hardness of tread (A)	63 Shore A

ELASTECH

UFP160X46-Ø12

EAN 4031582323368
Order number 00024982



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

