

# ELASTECH

UEP125X40-Ø8

EAN 4031582070354  
Order number 00027369



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	40 mm
Axle hole diameter	8.3 mm
Hub length	45 mm
Hardness of tread (A)	63 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	250 kg
Load capacity Static	500 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.463 kg

# ELASTECH

UEP125X40-Ø8

EAN 4031582070354  
Order number 00027369



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

