

SUPRATECH

PJO100X32-Ø12

EAN 4031582070224
Broj porudžbine 00026461

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	32 mm
dimenzija rupa osovina	12,3 mm
dužina glavcine	34,9 mm
Teškoća gazećeg omotac (A)	87 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Supratech
Tip kućišta	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	80 kg
Statički Nosivost	160 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,126 kg

SUPRATECH

PJO100X32-Ø12

EAN 4031582070224
Broj porudžbine 00026461



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

