

ELASTECH

UEP160X46-Ø20

EAN 4031582323245
Broj porudžbine 00026255

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	160 mm
Širina omotac	46 mm
dimenzija rupa osovina	20,1 mm
dužina glavcine	60 mm
Teškoća gazećeg omotac (A)	63 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,914 kg

ELASTECH

UEP160X46-Ø20

EAN 4031582323245
Broj porudžbine 00026255



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

