

# PURETECH

PVO100X35-Ø12

EAN 4031582321197  
Order number 00002025



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	35 mm
Axle hole diameter	12.1 mm
Hub length	44.4 mm
Hardness of tread (A)	80 Shore A

## PERFORMANCE

Roll performance	● ● ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	75 kg
Load capacity Static	150 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.195 kg

# PURETECH

PVO100X35-Ø12

EAN 4031582321197  
Order number 00002025



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

