

## PURETECH

PVO100X35-Ø12

EAN 4031582321197  
Broj porudžbine 00002025

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
dimenzija rupa osovina	12,1 mm
dužina glavcine	44,4 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

## PERFORMANSE

Performanse kotrljanja	● ● ○ ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	75 kg
Statički Nosivost	150 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,195 kg

# PURETECH

PVO100X35-Ø12

EAN 4031582321197  
Broj porudžbine 00002025



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

