

# MAXTECH

UAP125X32-Ø8

EAN 4031582322941  
Order number 00027145



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Axle hole diameter	8.3 mm
Hub length	36.5 mm
Hardness of tread (D)	40 Shore D

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.356 kg

# MAXTECH

UAP125X32-Ø8

EAN 4031582322941  
Order number 00027145



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

