

MAXTECH

UAP125X32-Ø8

EAN 4031582322941
Broj porudžbine 00027145

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ○ ○

Ishrana ● ● ● ● ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Maxtech

Tip kućišta Tocak

Standard EN12530 - Kastori uređaja

Nosivost na 3 km/h 160 kg

Statički Nosivost 320 kg

Temperaturni opseg (Minimalno) -25 °C

Opseg temperature (maksimalni) 80 °C

Ukupna težina 0,356 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	32 mm
dimenzija rupa osovina	8,3 mm
dužina glavcine	36,5 mm
Teškoća gazećeg omotac (D)	40 Šor D

MAXTECH

UAP125X32-Ø8

EAN 4031582322941
Broj porudžbine 00027145



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

