

## SUPRATECH

PJP075X25-Ø6

EAN 4031582070248

Broj porudžbine 00025287



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	75 mm
Širina omotac	25 mm
dimenzija rupa osovina	6,3 mm
dužina glavcine	28,2 mm
Teškoća gazećeg omotac (A)	87 Šora A

## PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Supratech
Tip kućišta	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	75 kg
Statički Nosivost	150 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,094 kg

# SUPRATECH

PJP075X25-Ø6

EAN 4031582070248  
Broj porudžbine 00025287



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

