

SUPRATECH

PJP100X32-Ø8

EAN 4031582070255
Order number 00026459



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polypropylene |
| Tread material | Thermoplastic rubber |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 100 mm |
| Tread width | 32 mm |
| Axle hole diameter | 8.3 mm |
| Hub length | 36.5 mm |
| Hardness of tread (A) | 87 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Supratech |
| Housing type | Wheel |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 100 kg |
| Load capacity Static | 200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall weight | 0.194 kg |

SUPRATECH

PJP100X32-Ø8

EAN 4031582070255
Order number 00026459



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

