

SUPRATECH

PJP100X32-Ø8

EAN 4031582070255

Broj porudžbine 00026459



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	100 mm
Širina omotac	32 mm
dimenzija rupa osovina	8,3 mm
dužina glavcine	36,5 mm
Teškoća gazećeg omotac (A)	87 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Supratech
Tip kućišta	Tocak
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,194 kg

SUPRATECH

PJP100X32-Ø8

EAN 4031582070255
Broj porudžbine 00026459



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

