

SUPRATECH

PJO125X32-Ø12 HL44,4

EAN 4031582320428
Order number 00001801



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Supratech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.175 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	125 mm
Tread width	32 mm
Axle hole diameter	12.2 mm
Hub length	44.4 mm
Hardness of tread (A)	87 Shore A

SUPRATECH

PJO125X32-Ø12 HL44,4

EAN 4031582320428
Order number 00001801



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

