

SUPRATECH

PJO125X32-Ø12 HL44,4

EAN 4031582320428

Broj porudžbine 00001801



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	32 mm
dimenzija rupa osovina	12,2 mm
dužina glavcine	44,4 mm
Teškoća gazećeg omotac (A)	87 Šora A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Supratech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,175 kg

SUPRATECH

PJO125X32-Ø12 HL44,4

EAN 4031582320428

Broj porudžbine 00001801



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

