

PURETECH

PVO160X40-Ø20

EAN 4031582321210
Order number 00023672



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ○ ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	135 kg
Load capacity Static	270 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.701 kg

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	160 mm
Tread width	40 mm
Axle hole diameter	20.1 mm
Hub length	58 mm
Hardness of tread (A)	80 Shore A

PURETECH

PVO160X40-Ø20

EAN 4031582321210
Order number 00023672



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

