

PURETECH

PVO160X40-Ø20

EAN 4031582321210
Broj porudžbine 00023672

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ○ ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ○ ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Tip kućišta	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	135 kg
Statički Nosivost	270 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,701 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	40 mm
dimenzija rupa osovina	20,1 mm
dužina glavcine	58 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

PVO160X40-Ø20

EAN 4031582321210
Broj porudžbine 00023672



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

