

DURATECH

TOO100X50-Ø15

EAN 4031582322484

Broj porudžbine 00801250



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	50 mm
dimenzija rupa osovina	15 mm
dužina glavcine	60 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	720 kg
Nosivost na 6 km/h	600 kg
Statički Nosivost	1200 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,388 kg

DURATECH

TOO100X50-Ø15

EAN 4031582322484
Broj porudžbine 00801250



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

