

DURATECH

TOO200X50-Ø20

EAN 4031582322545
Broj porudžbine 00801225

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	200 mm
Širina omotac	50 mm
dimenzija rupa osovine	20 mm
dužina glavnice	60 mm
Teškoća gazećeg omotac (D)	75 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	1200 kg
Nosivost na 6 km/h	1000 kg
Statički Nosivost	2000 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	1,219 kg

DURATECH

TOO200X50-Ø20

EAN 4031582322545
Broj porudžbine 00801225



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

