

# DURATECH

TOO150X50-Ø20

EAN 4031582322521  
Broj porudžbine 00801251



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavnice	60 mm
Teškoća gazećeg omotac (D)	75 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	960 kg
Nosivost na 6 km/h	800 kg
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,731 kg

# DURATECH

TOO150X50-Ø20

EAN 4031582322521  
Broj porudžbine 00801251



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

