

DURATECH

TOO250X50-Ø25

EAN 4031582322569
Order number 00801253



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	60 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1320 kg
Load capacity at 6 km/h	1100 kg
Load capacity Static	2200 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	1.54 kg

DURATECH

TOO250X50-Ø25

EAN 4031582322569
Order number 00801253



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

