

# DURATECH

TOP125X50-Ø20

EAN 4031582322682

Broj porudžbine 00801133



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	poliamid težak
materijal omotaca	Identično sa telom Tocak
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavcine	60 mm
Teškoća gazećeg omotac (D)	75 Šor D
Tip ležaja	6204

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Duratech
Tip kućišta	Tocak
Standard	EN12533 - Tockoviza teske terete
Nosivost na 4 km/h	840 kg
Nosivost na 6 km/h	700 kg
Statički Nosivost	1400 kg
Temperaturni opseg (Minimalno)	-40 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,805 kg

# DURATECH

TOP125X50-Ø20

EAN 4031582322682  
Broj porudžbine 00801133



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

