

ELASTECH

IEP125X50-Ø20

EAN 4031582319682

Broj porudžbine 00801254



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Aluminijum
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	precizini kuglicni lezaj
Boja Tocak	Crni mlaz (sličan RAL9005)
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	50 mm
dimenzija rupa osovina	20 mm
dužina glavnice	60 mm
Širina tela	50 mm
Teškoća gazećeg omotac (A)	68 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ● ●
Buka u pokretu	● ● ● ● ●
Ishrana	● ● ● ● ●
otpornost na rdju	● ● ● ● ●

OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Nosivost na 6 km/h	240 kg
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,922 kg

ELASTECH

IEP125X50-Ø20

EAN 4031582319682
Broj porudžbine 00801254



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

