

PURETECH

DIK050X19-Ø6

EAN 4031582070019
Order number 00000153



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	50 mm
Tread width	19 mm
Axle hole diameter	6.1 mm
Hub length	22.5 mm
Body width	19 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.086 kg

PURETECH

DIK050X19-Ø6

EAN 4031582070019
Order number 00000153



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

