

PURETECH

DIK 100X32-Ø8,1

EAN 4031582070156
Order number 00000161



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Axle hole diameter	8 mm
Hub length	36 mm
Body width	32 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall weight	0.444 kg

PURETECH

DIK 100X32-Ø8,1

EAN 4031582070156
Order number 00000161



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

