

PURETECH

DIK 150X32-Ø8,1

EAN 4031582070170
Order number 00000163



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	5.91 in
Tread width	1.26 in
Axle hole diameter	0.31 in
Hub length	1.42 in
Body width	1.26 in
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	1.98 lb

PURETECH

DIK 150X32-Ø8,1

EAN 4031582070170
Order number 00000163



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

