

PURETECH

UVH 080X35 HL46

EAN 4031582323627
Broj porudžbine 00002549

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	poliamid
materijal omotaca	Cvrsta guma crna
Nošenje	klizni lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Sa threadguard
Prečnik	80 mm
Širina omotac	35 mm
dimenzija rupa osovina	8,3 mm
dužina glavcine	46 mm
Širina tela	35 mm
Teškoća gazećeg omotac (A)	90 Šor A
Teškoća gazećeg omotac (D)	39 Šor D

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,218 kg

PURETECH

UVH 080X35 HL46

EAN 4031582323627
Broj porudžbine 00002549



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

