

PURETECH

PVR 100X35-Ø12

EAN 4031582321258
Broj porudžbine 00004952

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ● ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	75 kg
Statički Nosivost	150 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,233 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Širina tela	35 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

PVR 100X35-Ø12

EAN 4031582321258
Broj porudžbine 00004952



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

