

PURETECH

DIK 075X25-Ø6,1

EAN 4031582070149
Order number 00004955



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Axle hole diameter | 0.24 in |
| Hub length | 1.1 in |
| Body width | 0.98 in |
| Hardness of tread (A) | 80 Shore A |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Puretech |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 121.25 lb |
| Load capacity Static | 242.51 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 185 °F |
| Overall weight | 0.49 lb |

PURETECH

DIK 075X25-Ø6,1

EAN 4031582070149
Order number 00004955



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

