

## PURETECH

DIK 075X25-Ø6,1

EAN 4031582070149  
Broj porudžbine 00004955

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ● ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	55 kg
Statički Nosivost	110 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	85 °C
Ukupna težina	0,22 kg

## TOCAK

Materijal za telo	Čelik lista
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	konusi lezaj
Boja Tocak	plavo cinkovano
stitnici omotaca	Sa threadguard
Prečnik	75 mm
Širina omotac	25 mm
dimenzija rupa osovina	6 mm
duzina glavcine	28 mm
Širina tela	25 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

# PURETECH

DIK 075X25-Ø6,1

EAN 4031582070149  
Broj porudžbine 00004955



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

